



P.O. Number:

Date:

2018 Chamberlain Order Form For Total Camo Fabric Only

Billing Address

Contact Name:
Organization:
Street Address:
City, State:
ZIP Code:
Phone: Fax:
E-Mail:

Shipping Address (If Different)

Contact Name:
Organization:
Street Address:
City, State:
ZIP Code:
Phone: Fax:
E-Mail:

Qty	Part Number	Description	Unit Price	Line Total
	4000CHSS-TC	The Chamberlain Standard with Small Positioning Vest – an adaptive pediatric and adult positioning vehicle system (Weight range: 81 to 225 lbs). Small Positioning Vest (Total Camo) - for chest circumference between 25 and 32 inches and belly circumference less than 32 inches.		
	4000CHSM-TC	The Chamberlain Standard with Medium Positioning Vest – an adaptive pediatric and adult positioning vehicle system (Weight range: 81 to 225 lbs). Medium Positioning Vest (Total Camo) - for chest circumference between 30 and 37 inches and belly circumference less than 37 inches.		
	4000CHSL-TC	The Chamberlain Standard with Large Positioning Vest – an adaptive pediatric and adult positioning vehicle system (Weight range: 81 to 225 lbs). Large Positioning Vest (Total Camo) - for chest circumference between 35 and 44 inches and belly circumference less than 44 inches.		
	Please Note*:	One vest is included in the price of the Chamberlain. Pricing for additional vests is as follows.		
	2000CVS-TC	Small Positioning Vest (Total Camo) - for chest circumference between 25 and 32 inches and belly circumference less than 44 inches. *Price charged only when ordering additional vests.		
	2000CVM-TC	Medium Positioning Vest (Total Camo) - for chest circumference between 30 and 37 inches and belly circumference less than 44 inches. *Price charged only when ordering additional vests.		

	2000CVL-TC	Large Positioning Vest (Total Camo) - for chest circumference between 35 and 44 inches and belly circumference less than 44 inches. *Price charged only when ordering additional vests.		
		Optional Accessories		
	2000EUHR-TC	EZ-Up Head Rest (Total Camo Cover) – Supports head to limit side to side motion. To limit forward motion, choose a cap size from below:		
	See note to the right regarding the two cap options.	Note: There are two options for cap material. Total Camo or Khaki. The Khaki option is the coolest option for hot temperatures because it is single layer.		
	1000EUCS-K	EZ-Up Cap – Size Small (Khaki) - (Head Circumference: 17.5 – 19.5 inches)		
	1000EUCS-TC	EZ-Up Cap – Size Small (Total Camo) - (Head Circumference: 17.5 – 19.5 inches)		
	1000EUCM-K	EZ-Up Cap – Size Medium (Khaki) - (Head Circumference: 19.5 – 21.5 inches)		
	1000EUCM-TC	EZ-Up Cap – Size Medium (Total Camo) - (Head Circumference: 19.5 – 21.5 inches)		
	1000EUCL-K	EZ-Up Cap – Size Large (Khaki) - (Head Circumference: 21 – 23.25 inches)		
	1000EUCL-TC	EZ-Up Cap – Size Large (Total Camo) - (Head Circumference: 21 – 23.25 inches)		
	2000AB	Attachment Bracket Kit (for Vehicles without LATCH) – See Below**		
			Sub Total***	
Indiana Residents Only; Not Applicable to other States			Sales Tax (7%)	
			TOTAL	

* The “Chamberlain Standard” includes the following features:

- Torso Support System
- Anti-Slouching Leg Strap Assembly
- Positioning Vest (Small, Medium, or Large)
- Tether Extension Assembly

**** The Attachment Bracket Kit is designed for use in vehicles that do not have LATCH. The Chamberlain must be installed with LATCH or with the Attachment Bracket kit. All Vehicles 2003 and newer are equipped with LATCH in at least two rear seating positions, so there should be no installation issues for these vehicles and the Attachment Bracket will not be necessary. Many 2000 - 2002 models also have LATCH (See your vehicle owner’s manual to verify if LATCH is present).**

For vehicles without LATCH, the attachment bracket can only be used on vehicle seats that you can slide a ruler, or similar object, from the back side of the vehicle seat through the crack in the vehicle seat (where the seat bottom and seat back come together) through to the front side of the seat. This can usually be done in mini-vans and SUVs. Generally, the Attachment Bracket cannot be installed in the back seat of sedans. Installation of the Attachment Bracket Kit does require that a hole be drilled through the vehicle's floor board.

Please call Customer Service at 317-409-0148 with any questions regarding the installation of the Chamberlain.

*** Shipping charges – The cost of shipping "Best Way" will be added to Purchase Orders.

Please place orders by one of the following methods:

E-Mail: order@merrittcarseat.com

Phone: 317-409-0148

Fax: 317-893-2567

Thanks for Your Business!

[Merritt Manufacturing, Inc.](http://www.merrittcarseat.com)
www.merrittcarseat.com

P.O. Box 17152
Indianapolis, IN 46217